

PRODUCT-DETAILS

M12-C03

M12-C03 M12-8 female screw connector



General Information

Extended Product Type	M12-C03
Product ID	2TLA020055R1600
EAN	7350024452310
Catalog Description	M12-C03 M12-8 female screw connector
Long Description	Straight M12-8 female connector with cable screw connection. Cable diameter range 2.5–6.5 mm.

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	8544429090

Popular Downloads

Data Sheet, Technical Information	2TLC010001C0202
-----------------------------------	-----------------

Dimensions

Product Net Depth / Length	70 mm
----------------------------	-------

Product Net Height	20 mm
Product Net Width	20 mm
Product Net Weight	0.02 kg

Technical

Degree of Protection	IP65
Rated Control Supply Voltage (U _s)	24 V
Suitable For	JSHD4-2-AD JSHD4-2-AD-A JSHD4-3-AD JSHD4-3-AD-A JSHD4-3-AE JSHD4-4-AD JSHD4-4-AD-A JSHD4-5-AD JSHD4-5-AD-A Adam OSSD-Info M12-8 Adam OSSD-Reset M12-8

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	NoDecNee
--------------------------------	----------

Classifications

Object Classification Code	X
ETIM 4	EC002638 - Cable connector
ETIM 5	EC002638 - Cable connector
ETIM 6	EC002062 - Sensor-actuator connector
ETIM 7	EC002635 - Circular connector for field assembly (industrial connector)
UNSPSC	39121438
E-Number (Sweden)	3861438

Categories

Low Voltage Products and Systems → Control Products → Safety Products → Cables and Connectors

Low Voltage Products and Systems → Control Products → Safety Products → Safety Sensors, Switches and Locks Accessories

