

Energizer® Vision HD+ Focus Headlamp

HDD323


The *Energizer*® Vision HD+ Focus headlamp is another innovative headlamp solution within the *Energizer* headlamp line. Featuring LED technology, users get an extraordinarily bright, lightweight hands-free solution with ample run time. Custom optics offer exceptional direct and peripheral vision, making the *Energizer* Vision HD+ Focus a perfect light for home, work and outdoor activities. Featuring patented Digital Focus, users can easily broaden or narrow their field of vision with a simple button press. Memory Recall allows users to quickly access to their favorite focus setting next time the light is activated. With an adjustable head strap, water-resistant design and pivoting head to direct light exactly as needed, *Energizer* continues to deliver innovative lighting solutions.



Provides 400 Lumens of Light




Provides Run Time of 3 Hours



Shines Light on Objects 85 Meters Away



Sustains 1 Meter Drop Test



Water resistant IPX4 - Works even after splashing water on all sides

DESIGN BENEFITS

- ✓ Patented Digital Focus allows users to broaden or narrow the light beam
- ✓ Red LED mode allows users to preserve night vision
- ✓ Next Push Off to avoid unnecessary switch cycles
- ✓ Compact, lightweight design
- ✓ Water-resistant with shatterproof lens

LIGHT AND POWER SOURCE

- ✓ Features LED Technology
- ✓ Operates on 3 AAA Batteries

ELECTRICAL CHARACTERISTICS

Electrical Characteristics Nominal Power:
Power consumption 3.45W / Batteries AAA
Energizer E92 4.5V dc
LED Specifications: LED 3.0V cc / 1150 mA

CERTIFICATES AND COMPLIANCE

CE RoHS
EMC, EN62471, FCC



This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Tested according to ANSI/NEMA FL1 Standards. Results based on: *Energizer*® MAX, Alk / E92

PERFORMANCE BENEFITS

- ✓ Memory Recall feature permits to access preferred focus setting the next time the light is switched on
- ✓ Up to 4X brighter than standard LED technology
- ✓ Custom optics deliver exceptional direct and peripheral vision

SPECIFICATIONS

Weight Excluding Batteries:

53 Grams / 1.9 Ounces

Dimensions:

59mm x 49mm x 36mm / 2.3" x 1.9" x 1.4"

NUMBER OF OPERATING MODES: 5

Mode	Lumens	Runtime	Beam Distance
High	400	3	85
Low	45	35	30
Full Spot – Digital Focus	--	--	-
Full Flood – Digital Focus	--	--	-
Red	--	--	-