

## ETHERNET PORT CONNECTOR

Grace has your ethernet access solution.



P-R2-B3RX



P-R33-F3R0



P-R62-K3RF3



P-R2#2-M2RF5

### ELECTRICAL SPECIFICATIONS

- Low voltage (data), limited to 30 VDC
- High voltage supply (for computer use only)
- 120 VAC
- 230-240 VAC, 16A (CE only)

### MECHANICAL SPECIFICATIONS

- Housing: Cast Aluminium base
- Latch: Type 304 Stainless Steel (1CR18NI19)
- Cover: Polycarbonate, UV rated, V-O Flame rated
- Gasket Thermoplastic elastomer
- Insert Material: Acrylic UL94HB

### APPROVALS

UL Recognized: E207344 (Outdoor use)

CSA: LR110845 (not for interrupting circuit)

CE: EN61010/EN60950 (Foreign power outlets)

### Don't see what you're looking for?

Contact us at [sales@grace-eng.com](mailto:sales@grace-eng.com), call 1-800-280-9517 or visit [www.graceport.com](http://www.graceport.com) to chat with our customer service.

Sample Part No.:

**P - R 6 2 - K 3 R F 3**

**Ethernet Connector Code**

Connector Code	Description
R2	Category 5 RJ45 F/F Bulkhead
R13	Category 5e RJ45 F/IDT Bulkhead
R33	Category 5 Shielded RJ45 F/F Bulkhead
R62	Category 6 RJ45 F/F Bulkhead

**FOR MORE INFORMATION VISIT [GRACEPORT.COM](http://GRACEPORT.COM) OR CALL 1.800.280.9517**

**Warning:** Verify an electrical conductor has been de-energized using an adequately rated test instrument before working on it. Follow appropriate Energy Control (Lockout/Tagout) procedures as per OSHA Subpart S.

© Grace Engineered Products, Inc. All rights reserved. Specifications are subject to change with/without notice.



GP-R2R26R33R62-DS-EN 2001

