

Eminence


HF DRIVERS



SUPERTWEETER APT:50

Impedance	8 Ω
Power Rating	45Wrms @ 3.5kHz
(18dB/octave)	85Wrms @ 5.0kHz
Resonance	250Hz
Usable Frequency Range	3.5Hz - 20kHz
Recommend Crossover	3.5kHz
Sensitivity (1W @ 1m mounted to test horn)	105dB
Diaphragm Material	Phenolic
Le	0.15mH
Re	6.3 Ω
Depth	1.57", 40mm
Weight	1.5lbs., 682 kg.

NOTE: Using an Eminence PX Series crossover may slightly increase power handling capabilities.



SUPERTWEETER OPTIONS



APT:80


Dispersion	80° conical
Dimensions	3.4" X 3.4", 87mm X 87mm
Cut-out	3.15", 80mm
Depth	2.9", 73.6mm
Weight	1.6 lbs., 727g



APT:130

Dispersion	90° conical
Dimensions	5.23", 133mm
Cut-out	3.15", 80mm
Depth	2.9", 73.6mm
Weight	1.7 lbs., 772g

Not available in USA



APT:150

Dispersion	100 X 50
Dimensions	7.5" X 4.5", 191mm X 114mm
Cut-out	6.7" X 3.4", 170mm X 86mm
Depth	4.5", 114.3mm
Weight	1.6 lbs., 727g



APT:200

Dispersion	90 X 90
Dimensions	5.9" X 5.9", 150mm X 150mm
Cut-out	4.25" X 4.5", 108mm X 114mm
Depth	5.1", 129.5mm
Weight	2.5 lbs., 1136g