


IT18R**111-81821**

These cable ties are suitable for the identification and securing of cable bundles, saving valuable installation time by using just one product to both secure and identify. They can be marked either on-site or after bundling has taken place. They can be marked manually using the T82S series of indelible marker pens. In addition there is a large selection of labels available for marking.

One of the major benefits is the ability to both secure and identify cable bundles at different times.

Base Data**Colour**

Natural (NA)

Label E-Number Finland

13 721 70

Package Content

100

Quantity (Sold Unit / EDP)

100

Quantity per

Bag

Recommended Application Tool

MK20, MK3PNSP2, MK7P, MK7, MK3SP

Recommended Labels

TAG23-06TD1

Material and Specifications**Flammability**

UL94 V2

Material

Polyamide 6.6 (PA66)

Material Shortcut

PA66

Operating Temperature (Metric)

-40 °C to +85 °C Continuous, (+105 °C for 500 h)

Product Dimensions**Bundle Diameter max (Metric)**

22.0

Bundle Diameter min (Metric)

6.0

Height H (Metric)

8.0

Length L (Metric)

100.0

Minimum Tensile Strength (N)

80

Width W (Metric)

25.0

Width W2 (Metric)

2.3