


KR6G5

151-24600



Both CT & KR mounts give additional support to the cables by means of their curved design. Simple to install with a screw or bolt they give excellent security, particularly in areas of high vibration - when used in conjunction with the KR straps (see page ??) must offer one of the most vibration resistant fixings available.

Designed specifically for holding heavier cable bundles these mounting bases can be used in many industries from Agriculture to Truck manufacture, they offer a very secure fixing and can be used with a wide variety of heavy duty cable ties up to 7.6mm wide.

Base Data

Colour

Black (BK)

Package Content

100

Quantity per

Bag

Material and Specifications

Flammability

UL94 V2

Material

Polyamide 6.6 (PA66)

Material Shortcut

PA66

Operating Temperature (Metric)

-40 °C to +85 °C Continuous, (+105 °C for 500 h)

ROHS Conformity

TRUE

Product Dimensions

Cable Tie Width max. (metric)

6.0

Height H (Metric)

9.0

Height H2 (Metric)

4.0

Hole

4.5

Length L (Metric)

18.0

Width W (Metric)

12.0

