


KR8G5

151-24819



KR mounts give additional support to the cables by means of their curved design. Simple to install with a screw or bolt they give excellent security, particularly in areas of high vibration when used in conjunction with the KR straps. They must offer one of the most vibration resistant fixings available.

Designed specifically for holding heavier cable bundles these mounting bases can be used in many industries from agriculture to truck manufacture, they offer a very secure fixing and can be used with a wide variety of heavy duty cable ties up to 7.6mm wide.

Base Data**Colour**

Natural (NA)

Label E-Number Finland

13 708 47

Label E-Number Norway

13 300 26

Package Content

100

Quantity (Sold Unit / EDP)

100

Logistic and Packaging**Carton Quantity**

0

EAN code

4031026122403

Quantity of Europallet

0

Weight (kg) (Metric)

1.86 kg

Material and Specifications**Flammability**

UL94 V2

Material

Polyamide 6.6 (PA66)

Material Shortcut

PA66

Operating Temperature (Metric)

-40 °C to +85 °C Continuous, (+105 °C for 500 h)

ROHS Conformity

TRUE

Product Dimensions**Cable Tie Width max. (metric)**

8.0

Height H (Metric)

12.0

Height H2 (Metric)

5.5

Hole

6.5

Length L (Metric)

25.0

Width W (Metric)

14.5

© HellermannTyton 2006