

Ball valve QH-3/4

Part number: 9544

FESTO



Data sheet

Feature	Value
Type code	QH
Nominal pressure of fitting PN	30
Valve function	2/2 bistable
Pneumatic connection 1	G3/4
Pneumatic connection 2	G3/4
Actuation type	Manual
Type of mounting	Line installation
Standard nominal flow rate	21000 l/min
Nominal width	20 mm
Ambient temperature	-20 °C ... 180 °C
Housing material	Brass
Operating medium	Water Compressed air as per ISO 8573-1:2010 [7:-:-]

Feature	Value
Sealing principle	Soft
Design	Ball valve
Symbol	00991458
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)