

Push-in T-fitting NPQP-T-R12-Q12-FD

Part number: 133080

FESTO



Data sheet

| Feature | Value |
|--|--|
| Size | Standard |
| Nominal width | 6.9 mm |
| Type code | NPQP |
| Pack size | 1 |
| Design | Push-pull principle |
| Temperature-dependent operating pressure | -0.95 bar ... 10 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Information on operating and pilot media | Operation with oil lubrication possible |
| Corrosion resistance class (CRC) | 4 - Particularly high corrosion stress |
| For use in the food industry | See supplementary material information |
| Ambient temperature | -20 °C ... 60 °C |
| Product weight | 28 g |
| Pneumatic connection 1 | R1/2 |
| Pneumatic connection 2 | for pneumatic tubing outside diameter 12 mm |
| Note on materials | Contains paint-wetting impairment substances RoHS-compliant |
| Housing material | PP |
| Material of tube retaining claw | High-alloy stainless steel |