


# Needle valve GRO-1/8-B

Part number: 151216

FESTO



## Data sheet

Feature	Value
Type code	GRO
Valve function	Flow control function
Pneumatic connection 1	G1/8
Pneumatic connection 2	G1/8
Adjusting element	Knurled screw
Type of mounting	With through-hole Optionally: Front panel mounting
Standard nominal flow rate in flow control direction	210 l/min
Operating pressure	0 bar ... 10 bar
Ambient temperature	-20 °C ... 60 °C
Housing material	Wrought aluminum alloy
Nominal width	3 mm
Mounting position	Any
Symbol	00991454
Explosion prevention and protection	Zone 21 (ATEX) Zone 1 (ATEX) Zone 22 (ATEX) Observe the information on the certificate Zone 2 (ATEX)
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Temperature of medium	-20 °C ... 60 °C
Product weight	31 g

<b>Feature</b>	<b>Value</b>
Note on materials	RoHS-compliant
Seals material	NBR
Material of adjusting screw	High-alloy steel
Nut material	Wrought aluminum alloy
Sleeve material	POM