


# Non return valve H-QS-8

Part number: 153464

FESTO



## Data sheet

Feature	Value
Type code	H
Housing colour	Black
Valve function	Non-return function
Pneumatic connection 1	QS-8
Pneumatic connection 2	QS-8
Type of mounting	Line installation
Standard nominal flow rate	681 l/min
Operating pressure	-1 bar ... 10 bar
Ambient temperature	0 °C ... 60 °C
Housing material	Aluminum, anodized
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Symbol	00991455
Min. differential pressure, opening	0.1 bar
Min. differential pressure, closing	0.2 bar
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Product weight	21 g
Note on materials	RoHS-compliant Free of copper and PTFE