


Quick exhaust valve VBQF-U-G14-E

Part number: 548001

FESTO



Data sheet

| Feature | Value |
|--|--|
| Type code | VBQF-U |
| Valve function | Quick exhaust |
| Selection of additional function | With pneumatic muffler |
| Pneumatic connection 1 | G1/4 |
| Pneumatic connection 2 | G1/4 |
| Type of mounting | Screw-in |
| Standard flow rate exhaust 6-> 0 bar | 2500 l/min |
| Standard nominal flow rate pressurization 6->5 bar | 960 l/min |
| Operating pressure | 0.5 bar ... 10 bar |
| Ambient temperature | -20 °C ... 80 °C |
| Housing material | Die-cast zinc Die-cast aluminum |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Nominal width | 7 mm |
| Mounting position | Any |
| Symbol | 00991460 |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| Temperature of medium | -20 °C ... 80 °C |
| Noise level | 75 dB(A) |
| Product weight | 226 g |
| Note on materials | RoHS-compliant |
| Seals material | NBR |