

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0150180105](#)
Status: **Active**
Overview: [Premo-Flex Cable Jumpers](#)
Description: 0.50mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 10 Circuits, 152.00mm Cable Length, Gold (Au) Plating, with Ears

Documents:

| | |
|---|--|
| Drawing (PDF) | Datasheet (PDF) |
| Product Specification 150180001-000 (PDF) | RoHS Certificate of Compliance (PDF) |

General

| | |
|-------------------------|--|
| Product Family | Cable |
| Series | 15018 |
| Comments | Same Side Contacts, Type A |
| Crimp Quality Equipment | Yes |
| Overview | Premo-Flex Cable Jumpers |
| Product Name | Premo-Flex FFC Jumper |
| UPC | 193264329519 |

Physical

| | |
|-------------------------------|-----------------|
| Cable Length | 152.00mm |
| Circuits (Loaded) | 10 |
| Net Weight | 0.680/g |
| Packaging Type | Bag |
| Pitch - Mating Interface | 0.50mm |
| Temperature Range - Operating | -40° to +105°C |
| Wire Size AWG | N/A |
| Wire/Cable Type | Flat Flex Cable |

Electrical

| | |
|-------------------------------|--------|
| Current - Maximum per Contact | 0.5A |
| Voltage - Maximum | 60V AC |

Material Info

Reference - Drawing Numbers

| | |
|-----------------------|---------------|
| Product Specification | 150180001-000 |
| Sales Drawing | SD-15018-001 |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ECHA_01_2020 (16
January 2020

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[15018 Series](#)

Mates With

Easy-On FFC/FPC Connector [5051101092](#)