

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0150180215](#)
Status: **Active**
Overview: [Premo-Flex Cable Jumpers](#)
Description: 0.50mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 20 Circuits, 152.00mm Cable Length, Gold (Au) Plating, with Ears

Documents:

[Drawing \(PDF\)](#) [Datasheet \(PDF\)](#)
[Product Specification 150180001-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family [Cable](#)
 Series [15018](#)
 Comments [Same Side Contacts, Type A](#)
 Crimp Quality Equipment [Yes](#)
 Overview [Premo-Flex Cable Jumpers](#)
 Product Name [Premo-Flex FFC Jumper](#)
 UPC [193264330515](#)

Physical

Cable Length [152.00mm](#)
 Circuits (Loaded) [20](#)
 Net Weight [1.360/g](#)
 Packaging Type [Bag](#)
 Pitch - Mating Interface [0.50mm](#)
 Temperature Range - Operating [-40° to +105°C](#)
 Wire Size AWG [N/A](#)
 Wire/Cable Type [Flat Flex Cable](#)


Electrical

Current - Maximum per Contact [0.5A](#)
 Voltage - Maximum [60V AC](#)

Material Info

Reference - Drawing Numbers

Product Specification [150180001-000](#)
 Sales Drawing [SD-15018-001](#)



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ECHA_01_2020 (16
 January 2020

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[15018 Series](#)

Mates With

Easy-On FFC/FPC Connector [5051102091](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION