


# GS1AN11

Auxiliary contacts, TeSys GS, 1NC + 1NO,  
instantaneous, left side mounting, for GS1-GS2  
with front/right handle

Product availability : Non-Stock - Not normally stocked in distribution facility



## Main

Range of product	TeSys
Device short name	GS1AN
Product or component type	Auxiliary contact
Contact application	O and I position signalling
Contacts type and composition	1 NC + 1 NO
Contact operation	Instantaneous
[I <sub>th</sub> ] conventional free air thermal current	20 A 104 °F (40 °C)
[I <sub>e</sub> ] rated operational current	1 A 220 V DC-13 10 A 230 V AC-15 12 A 127 V AC-15 4 A 48 V DC-13 6 A 440 V AC-15 8 A 400/415 V AC-15 1.2 A 110 V DC-13

## Complementary

Range compatibility	TeSys GS switch-disconnector-fuse
Mechanical durability	30000 cycles
Electrical durability	30000 cycles AC-15
Switch rated current	1250 A 160 A 400 A 50 A 63 A 800 A 250 A 315 A 600 A 125 A 100 A 60 A 200 A 630 A
Fuse type	NFC

	DIN BS
Type of operating handle	Direct frontal Direct right side External right side External frontal
Net weight	0.29 lb(US) (0.132 kg)

### Ordering and shipping details

Category	22640 - IEC DISCONNECT-GS1,LK3
Discount Schedule	I11
GTIN	00785901367772
Returnability	No
Country of origin	FR

### Offer Sustainability

REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>

### Contractual warranty

Warranty	18 months
----------	-----------