

Rod clevis
SG-M12X1,25
Part number: 6145



Data sheet

Feature	Value
Size	M12x1.25
Type code	SG
Conforms to standard	ISO 8140 DIN 71752
Threaded connection	Internal thread M12x1.25
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-40 °C ... 150 °C
Product weight	166 g
Note on materials	Free of copper and PTFE RoHS-compliant
Bolt material	Galvanized Steel
Clevis material	Steel Galvanized
Nut material	Steel Galvanized