

# Distributor block FR-4-3/8-B

Part number: 6703

FESTO



## Data sheet

| Feature                                         | Value                                                              |
|-------------------------------------------------|--------------------------------------------------------------------|
| Nominal width                                   | 15 mm                                                              |
| Type code                                       | FR                                                                 |
| Mounting position                               | Any                                                                |
| Operating pressure for entire temperature range | 0 bar ... 16 bar                                                   |
| Operating medium                                | Compressed air as per ISO 8573-1:2010 [7:-:-]                      |
| Information on operating and pilot media        | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)                | 0 - No corrosion stress                                            |
| Ambient temperature                             | -10 °C ... 80 °C                                                   |
| Product weight                                  | 75 g                                                               |
| No. of outlets                                  | 3                                                                  |
| No. of supply lines                             | 1                                                                  |
| Pneumatic connection 1                          | Internal thread G3/8                                               |
| Pneumatic connection 2                          | Internal thread G3/8                                               |
| Note on materials                               | RoHS-compliant                                                     |
| Housing material                                | Die-cast aluminum                                                  |