


# Connecting cable SIM-M8-3WD-5-PSL-PU

Part number: 159425

FESTO



## Data sheet

Feature	Value
Type code	SIM
Conforms to standard	EN 61076-2-104 EN 61984
Ready status indication	LED green
Switching status indication	LED yellow
Electrical connection	3-pin/3-wire Angled socket/open end M8x1 / -
DC operating voltage range	10 V ... 30 V
Current rating at 40°C	4 A
Surge resistance	0.8 kV
Cable length	5 m
Cable characteristic	Standard
Connector cable test conditions	Test conditions on request Flexural strength: as per Festo standard Cable chain: 5 million cycles, bending radius 75 mm
Cable diameter	4.5 mm
Cable design	3 x 0.25 mm <sup>2</sup>
Nominal conductor cross section	0.25 mm <sup>2</sup>
Wire insulation color code	Black Brown Blue
Degree of protection	IP65 IP68
Ambient temperature	-25 °C ... 80 °C
Ambient temperature with flexible cable installation	-5 °C ... 80 °C
CE marking (see declaration of conformity)	As per EU RoHS directive
Note on materials	RoHS-compliant Free of phosphoric acid ester Halogen-free
Contamination level	3
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Material of cable sheath	TPE-U(PU)
Color cable sheath	Gray
Housing material	TPE-U(PU)
Housing colour	Black
Material of union nut	Nickel-plated Brass
Insulating sheath material	PP

Feature	Value
Symbol	00995371