


Precision pressure regulator LRP-1/4-4

Part number: 159501

FESTO



Data sheet

Feature	Value
Type code	LRP
Actuator lock	Rotary knob with detent
Mounting position	Any
Design	Pilot-controlled precision diaphragm regulator
Controller function	Outlet pressure constant With secondary exhausting
Symbol	00991540
Pressure gauge	G1/8 prepared
Operating pressure	1 bar ... 12 bar
Pressure regulation range	0.05 bar ... 4 bar
Max. pressure hysteresis	0.02 bar
Standard nominal flow rate	2000 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gas
Information on operating and pilot media	Operation with oil lubrication not possible
Temperature of medium	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Product weight	310 g
Type of mounting	Line installation Front panel mounting With accessories
Pneumatic connection 1	G1/4
Pneumatic connection 2	G1/4
Note on materials	RoHS-compliant
Seals material	NBR
Housing material	Aluminum