

Air reservoir CRVZS-0.1

Part number: 160233

FESTO



Data sheet

Feature	Value
Volume	0.1 l
Type code	CRVZS
Mounting position	Any
Conforms to standard	AD 2000
Symbol	00991528
Operating pressure	-0.95 bar ... 16 bar
Certificate issuing authority	TSSACRNOH17477.5C
Operating medium	Compressed air as per ISO 8573-1:2010 [-:--] Nitrogen
Corrosion resistance class (CRC)	3 - High corrosion stress
For use in the food industry	See supplementary material information
Temperature of medium	-10 °C ... 100 °C
Ambient temperature	-10 °C ... 100 °C
Certification	CRN German Technical Control Board (TÜV)
Max. tightening torque for connecting thread	15 Nm
Product weight	226 g
Type of mounting	Fixing clips
Pneumatic connection	G1/8
Note on materials	RoHS-compliant Free of copper and PTFE
Air reservoir material	High-alloy stainless steel
Fixing clips material	High-alloy stainless steel