

Foot mounting HNC-40

Part number: 174370

FESTO



Data sheet

| Feature | Value |
|----------------------------------|---|
| Size | 40 |
| Type code | HNC |
| Based on norm | ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290) |
| Conforms to standard | ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| Ambient temperature | -40 °C ... 150 °C |
| Product weight | 193 g |
| Note on materials | RoHS-compliant Free of copper and PTFE |
| Mounting material | Galvanized Steel |
| Material of screws | Steel Galvanized |