

Foot mounting HNC-50

Part number: 174371

FESTO



Data sheet

Feature	Value
Size	50
Type code	HNC
Based on norm	ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Conforms to standard	ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	-40 °C ... 150 °C
Product weight	353 g
Note on materials	RoHS-compliant Free of copper and PTFE
Mounting material	Galvanized Steel
Material of screws	Galvanized Steel