


# Clevis flange SNC-40

Part number: 174384

FESTO



## Data sheet

Feature	Value
Size	40
Type code	SNC
Based on norm	ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-40 °C ... 150 °C
Product weight	141 g
Note on materials	Free of copper and PTFE RoHS-compliant
Mounting material	Die-cast aluminum
Bolt material	Galvanized Steel
Material of screws	Galvanized Steel
Fuse material	Spring steel Galvanized