


Clevis flange SNCB-80

Part number: 174394

FESTO



Data sheet

Feature	Value
Size	80
Type code	SNCB
Based on norm	ISO 15552
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-40 °C ... 90 °C
Product weight	636 g
Note on materials	RoHS-compliant Free of copper and PTFE
Mounting material	Die-cast aluminum
Bolt material	Steel, galvanized
Material of bearing	Polymer
Material of screws	Steel, galvanized
Fuse material	Spring steel, galvanized