


Pressure regulator MS4-LR-1/8-D7-AS

Part number: 529425

FESTO



Data sheet

| Feature | Value |
|--|--|
| Size | 4 |
| For use in the food industry | See supplementary material information |
| Type code | MS4-LR |
| Series | MS |
| Actuator lock | can be closed with accessories Rotary knob with detent |
| Mounting position | Any |
| Design | Directly controlled diaphragm regulator |
| Controller function | Outlet pressure constant With return flow function With secondary exhausting |
| Symbol | 00991558 |
| Pressure gauge | with pressure gauge |
| Operating pressure | 0.8 bar ... 14 bar |
| Pressure regulation range | 0.5 bar ... 12 bar |
| Max. pressure hysteresis | 0.25 bar |
| Standard nominal flow rate | 1000 l/min |
| Operating medium | Inert gas Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| Storage temperature | -10 °C ... 60 °C |
| Temperature of medium | -10 °C ... 60 °C |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 225 g |
| Type of mounting | Optionally: Line installation Front panel mounting With accessories |
| Pneumatic connection 1 | G1/8 |
| Pneumatic connection 2 | G1/8 |
| Note on materials | RoHS-compliant |
| Material of sub-base | Die-cast aluminum |
| Material of operator panel | PA POM |
| Seals material | NBR |

| Feature | Value |
|--------------------------------|-------------------|
| Compressed air filter material | PE |
| Housing material | Die-cast aluminum |
| Diaphragm material | NBR |