


# Air reservoir CRVZS-20

Part number: 534845

FESTO



## Data sheet

Feature	Value
Volume	20 l
Type code	CRVZS
Mounting position	Condensate drain downwards
Conforms to standard	AD 2000
Symbol	00991474
Operating pressure	-0.95 bar ... 16 bar
Certificate issuing authority	CRNOH15669.5C
Operating medium	Compressed air as per ISO 8573-1:2010 [-:--] Nitrogen
CE marking (see declaration of conformity)	as per EU pressure equipment directive
Corrosion resistance class (CRC)	3 - High corrosion stress
For use in the food industry	See supplementary material information
Temperature of medium	-10 °C ... 100 °C
Ambient temperature	-10 °C ... 100 °C
Certification	CRN German Technical Control Board (TÜV)
Max. tightening torque for connecting thread	130 Nm
Max. tightening torque for condensate drain	27 Nm
Product weight	10208 g
Type of mounting	With through-hole
Condensate drain connection	G3/8
Pneumatic connection	G1
Note on materials	RoHS-compliant Free of copper and PTFE
Air reservoir material	High-alloy stainless steel