

Solenoid coil MSFG-24-EX

Part number: 536931

FESTO



Data sheet

Feature	Value
Type code	MSFG
Mounting position	Any
Min. pick-up time	10 ms
Duty cycle	100%
Coil characteristics	24 V DC: 4.5 W
Permissible voltage fluctuations	+/- 10 %
ATEX category gas	II 3G
Type of ignition protection for gas	Ex nA IIC T4 X Gc
ATEX category for dust	II 3D
Type of (ignition) protection for dust	Ex tc IIIC T130°C X Dc IP65
Explosion protection certification outside the EU	EPL Gc (CN) EPL Dc (CN)
Explosive ambient temperature	-5°C ≤ Ta ≤ +40°C
Explosion prevention and protection	Zone 22 (ATEX) Zone 2 (CN) Zone 22 (CN) Zone 2 (ATEX)
CE marking (see declaration of conformity)	as per EU explosion protection directive (ATEX)
Degree of protection	IP65
Ambient temperature	-5 °C ... 40 °C
Max. tightening torque of socket	0.4 Nm
Product weight	55 g
Electrical connection	Plug flags with connection diagram as per Festo standard for MSSD-F 3-pin
Type of mounting	With knurled nut
Note on materials	RoHS-compliant
Solenoid coil material	Steel Duroplast Copper
Material of winding	Copper