


Proximity sensor SMT-10M-NS-24V-E-2,5-L-OE

Part number: 551377

FESTO



Data sheet

Feature	Value
Type code	SMT
Electrical connection 1, connection technology	Open end
Electrical connection 1, connection type	Cable
KC characters	KC EMC
Repetition accuracy	0.2 mm
Electrical connection 1, number of pins/wires	3
Design	for round slot
Conforms to standard	EN 60947-5-2
Symbol	00991149
Certification	RCM compliance mark
CE marking (see declaration of conformity)	As per EU EMC directive
Special features	Oil-resistant
Note on materials	RoHS-compliant Free of copper and PTFE Halogen-free
Measured variable	Position
Measuring principle	Magneto-resistive
Ambient temperature	-40 °C ... 70 °C
Switching output	NPN
Switching element function	N/O contact
On time	≤1.3 ms
Switch-off time	≤1.4 ms
Max. switching frequency	150 Hz
Max. output current	100 mA
Max. output current in mounting kits	50 mA
Max. switching capacity DC	2.8 W
Max. switching capacity DC in mounting kits	1.5 W
Voltage drop	≤1.5 V
Short-circuit protection	yes
Overload protection	Available
Rated operating voltage DC	24 V
DC operating voltage range	5 V ... 30 V
Reverse polarity protection	for all electrical connections
Connection outlet orientation	Longitudinal

Feature	Value
Connector cable test conditions	Torsional resistance: > 300 000 cycles, $\pm 270^\circ/0.1$ m Flexural strength: as per Festo standard Cable chain: 5 million cycles, bending radius 28 mm Test conditions on request
Cable length	2.5 m
Cable characteristic	Suitability for energy chains/robot applications
Material of cable sheath	TPE-U(PUR)
Type of mounting	Can be inserted in slot from above Screwed tightly
Max. tightening torque	0.4 Nm
Mounting position	Any
Product weight	16.8 g
Housing material	PA-reinforced High-alloy stainless steel
Switching status indication	LED yellow
Ambient temperature with flexible cable installation	-20 °C ... 70 °C
Degree of protection	IP65 IP68