


Proximity sensor SMT-8M-A-ZS-24V-E-5,0-OE-EX2

Part number: 574341

FESTO



Data sheet

Feature	Value
Type code	SMT
Electrical connection 1, connection technology	Open end
Electrical connection 1, connection type	Cable
KC characters	KC EMC
Repetition accuracy	0.2 mm
Electrical connection 1, number of pins/wires	2
Design	for T-slot
Based on norm	EN 60947-5-2
Symbol	00991623
Certification	c UL us - Listed (OL) RCM compliance mark
CE marking (see declaration of conformity)	As per EU EMC directive as per EU explosion protection directive (ATEX) As per EU RoHS directive
Explosion prevention and protection	Zone 22 (ATEX) Zone 2 (ATEX)
ATEX category gas	II 3G
Type of ignition protection for gas	Ex nA IIC T4 X Gc
ATEX category for dust	II 3D
Type of (ignition) protection for dust	Ex tc IIIC T120°C X Dc
Explosive ambient temperature	-40°C ≤ Ta ≤ +70°C
Special features	Oil-resistant
Note on materials	Halogen-free Free of copper and PTFE RoHS-compliant
Measured variable	Position
Measuring principle	Magneto-resistive
Ambient temperature	-40 °C ... 85 °C
Switching output	Non-contact, 2-wire
Switching element function	N/O contact
On time	≤ 1 ms
Switch-off time	≤ 1 ms
Max. switching frequency	180 Hz
Max. output current	80 mA
Max. output current in mounting kits	50 mA
Max. switching capacity DC	1.9 W
Max. switching capacity DC in mounting kits	1.2 W

Feature	Value
Voltage drop	<6 V
Short-circuit protection	yes
Overload protection	Available
Rated operating voltage DC	24 V
DC operating voltage range	7 V ... 30 V
Reverse polarity protection	for all electrical connections
Connection outlet orientation	Longitudinal
Connector cable test conditions	Flexural strength: as per Festo standard Torsional resistance: > 300 000 cycles, ±270°/0.1 m Cable chain: 5 million cycles, bending radius 28 mm Test conditions on request
Cable length	5 m
Cable characteristic	Suitability for energy chains/robot applications
Color cable sheath	Gray
Material of cable sheath	TPE-U(PUR)
Type of mounting	Can be inserted in slot from above Screwed tightly
Max. tightening torque	0.6 Nm
Mounting position	Any
Product weight	57.1 g
Housing colour	Black
Housing material	High-alloy stainless steel PA-reinforced
Switching status indication	LED yellow
Function reserve indication	LED orange
Ambient temperature with flexible cable installation	-20 °C ... 85 °C
Degree of protection	IP65 IP68 IP69K