

# Cover plate VABB-L1-18

Part number: 574482

FESTO



## Data sheet

Feature	Value
Width dimension	19 mm
Type code	VABB
Operating pressure	-0.9 bar ... 10 bar
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Certification	RCM compliance mark c UL us - Recognized (OL) c CSA us (OL)
Max. tightening torque for valve mounting	1.18 Nm
Product weight	50 g
Note on materials	RoHS-compliant
Cover plate material	Wrought aluminum alloy