



Overview

| | |
|----------------------|---|
| Model Name | APC Smart-UPS 1500VA LCD 120V TAA |
| Includes | CD with software , Documentation CD , Smart UPS signalling RS-232 cable , USB cable |
| Standard Lead Time | Usually Ships within 2 Weeks |
| Product Distribution | Canada , United States |

Output

| | |
|----------------------------------|---------------------------------|
| Output Power Capacity | 1000 Watts / 1440 VA |
| Max Configurable Power (Watts) | 1000 Watts / 1440 VA |
| Nominal Output Voltage | 120V |
| Output Voltage Distortion | Less than 5% |
| Output Frequency (sync to mains) | 50/60Hz +/- 3 Hz |
| Output Frequency (sync to mains) | Line Interactive |
| Waveform Type | Sine wave |
| Output Connections | (8) NEMA 5-15R (Battery Backup) |

Input

| | |
|--|----------------------------------|
| Nominal Input Voltage | 120V |
| Input Frequency | 50/60 Hz +/- 3 Hz (auto sensing) |
| Input Connections | NEMA 5-15P |
| Cord Length | 1.83 meters |
| Input voltage range for main operations | 82 - 144 V |
| Input voltage adjustable range for mains operation | 75 - 154V |

Batteries & Runtime

| | |
|-----------------------|--|
| Battery Type | Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof |
| Typical recharge time | 3 hour(s) |
| Replacement Battery | RBC7 |
| RBC Quantity | 1 |

Communications & Management

| | |
|---|---|
| Interface Port(s) | SmartSlot , USB |
| Available SmartSlot™ Interface Quantity | 1 |
| Control panel | Multi-function LCD status and control console |
| Audible Alarm | Alarm when on battery : distinctive low battery alarm : configurable delays |
| Emergency Power Off (EPO) | Optional |

Surge Protection and Filtering

| | |
|---------------------|--|
| Surge energy rating | 459 Joules |
| Filtering | Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449 |

Physical

| | |
|------------------|----------|
| Maximum Height | 219.0 mm |
| Maximum Width | 171.0 mm |
| Maximum Depth | 439.0 mm |
| Net Weight | 24.09 kg |
| Shipping Weight | 27.23 kg |
| Shipping Height | 376.0 mm |
| Shipping Width | 328.0 mm |
| Shipping Depth | 595.0 mm |
| Color | Black |
| Units per Pallet | 24.0 |

Environmental

| | |
|---|----------------|
| Operating Environment | 0 - 40 °C |
| Operating Relative Humidity | 0 - 95 % |
| Operating Elevation | 0-3000 meters |
| Storage Temperature | -15 - 45 °C |
| Storage Relative Humidity | 0 - 95 % |
| Storage Elevation | 0-15000 meters |
| Audible noise at 1 meter from surface of unit | 45.000 dB |
| Online Thermal Dissipation | 135.000 BTU/hr |

Conformance

| | |
|-----------------------------|--|
| Approvals | TAA compliance , UL 1778 , cUL Listed |
| Standard warranty | 3 years repair or replace (excluding battery) and 2 year for battery |
| Equipment protection policy | Lifetime : \$150000 |

Sustainable Offer Status

| | |
|-------|--------------------------|
| RoHS | Compliant |
| REACH | REACH: Contains No SVHCs |