



General ordering data

Order No.	9510210000
Part designation	Klippon POK 1 Ex
Version	EXI enclosure, 56 mm, 75 mm, 80 mm, glass fibre-reinforced polyester
EAN	4008190498498
Qty	1

Dimensions

Fixing dimension, height	45 mm
Fixing dimension, width	68 mm
Length	75 mm
Height	56 mm
Width	80 mm

General details

Enclosure fixing	Holes 4 mm
Sealing material	Polyurethane und chloroprene
Cover fixing	4 stainless steel M4 screws
Colour	grey
Class of protection to EN 60529	IP 66
Weight	230 g
Ambient temperature, min.	-40 °C
Ambient temperature, max.	90 °C

Screwed cable glands top/bottom

M 12	4
M 20	1
M 16	2
M 25	1
Side of enclosure	Top / Bottom

Screwed cable glands, left/right

M12	1
M16	1
M20	1
Side of enclosure	left / right

Classifications

ETIM 2.0	EC000520
ETIM 3.0	EC000049
eClass 4.1	27-14-12-06
eClass 5.0	27-18-05-02
eClass 5.1	27-18-05-02

Related products

Length	Height	Width
75 mm	56 mm	80 mm