



General ordering data

| | |
|------------------|--|
| Version | EXI enclosure, 91 mm, 120 mm, 220 mm, glass fibre-reinforced polyester |
| Order No. | 9510240000 |
| Part designation | Klippon POK 5 Ex |
| EAN | 4008190498580 |
| Qty | 1 |

Dimensions

| | |
|--------------------------|--------|
| Fixing dimension, height | 82 mm |
| Fixing dimension, width | 204 mm |
| Length | 120 mm |
| Height | 91 mm |
| Width | 220 mm |

General details

| | |
|---------------------------------|------------------------------|
| Sealing material | Polyurethane und chloroprene |
| Enclosure fixing | Holes 6 mm |
| Cover fixing | 4 stainless steel M6 screws |
| Colour | grey |
| Class of protection to EN 60529 | IP 66 |
| Weight | 1060 g |
| Ambient temperature, min. | -40 °C |
| Ambient temperature, max. | 90 °C |

Screwed cable glands top/bottom

| | |
|-------------------|--------------|
| M 32 | 4 |
| M 16 | 14 |
| M 40 | 3 |
| M 20 | 12 |
| M 25 | 5 |
| M 12 | 24 |
| Side of enclosure | Top / Bottom |

Screwed cable glands, left/right

| | |
|-------------------|--------------|
| M16 | 4 |
| M20 | 3 |
| M25 | 1 |
| M32 | 1 |
| M12 | 8 |
| Side of enclosure | left / right |

Classifications

| | |
|------------|-------------|
| ETIM 2.0 | EC000520 |
| ETIM 3.0 | EC000049 |
| eClass 4.1 | 27-14-12-06 |
| eClass 5.0 | 27-18-05-02 |
| eClass 5.1 | 27-18-05-02 |

Related products

| Length | Height | Width |
|--------|--------|--------|
| 120 mm | 91 mm | 220 mm |