



### General ordering data

Order No.	1565410000
Part designation	Klippon POK 51
Version	Housings, 90 mm, 160 mm, 160 mm, glass fibre-reinforced polyester
EAN	4032248414871
Qty	1

### Dimensions

Fixing dimension, width	140 mm
Fixing dimension, height	110 mm
Height	90 mm
Length	160 mm
Width	160 mm

### General details

Enclosure fixing	Holes 6 mm
Sealing material	Polyurethane und chloroprene
Cover fixing	4 stainless steel M6 screws
Version cover	closed
Class of protection to EN 60529	IP 66
Weight	1290 g
Ambient temperature, min.	-40 °C
Ambient temperature, max.	90 °C

### Screwed cable glands top/bottom

M 25	3
M 12	15
M 40	2
M 16	12
M 32	2
M 20	6
Side of enclosure	Top / Bottom

**Screwed cable glands, left/right**

M16	6
M20	4
M25	2
M32	2
M12	11
M40	1
Side of enclosure	left / right

**Classifications**

ETIM 2.0	EC000058
ETIM 3.0	EC000058
eClass 4.1	27-14-12-06
eClass 5.0	27-14-91-07
eClass 5.1	27-14-91-07

**Related products**

Height	Length	Width
90 mm	160 mm	160 mm