

Acer C200 - DLP projector - 200 lumens(MR.JQC11.001)

Acer C200 - DLP projector - LED - 200 lumens - WVGA (854 x 480) - 16:9

From office presentations to catching a movie on your break, the C2 series helps you make your way through a busy day. Connect with ease as you project longer and wait less.



Key Selling Points

- The power of sound
- Project cable-free
- Superior lighting
- Smartphone compatibility
- No more waiting
- Friend to the environment

Product Features

Anytime, anywhere

The C2 series is ideal for your travel needs.

Charge up

Enjoy full-length feature films without recharging with hours of renewable battery life.

The power of sound

Set the tone with full, vibrant audio from the on-board dual speaker sound system.

Project cable-free

Break free from burdensome, unsightly cables and project with ease using the wireless dongle.

Superior lighting

LED lighting lets you enjoy a wider color gamut and greater bulb durability.

Smartphone compatibility

Charge your smartphone device and project all your favorite photos, music and videos with the convenient MHL port.

No more waiting

The LED light source provides immediate on/off functionality, saving you valuable time and keeping you on the move.

Friend to the environment

Acer EcoProjection reduces power consumption and can extend your lamp life.

Main Specifications

Product Description	Acer C200 - DLP projector
Device Type	DLP projector
Built-in Devices	Lithium-ion battery (6700 mAh)
Brightness	200 lumens
Contrast Ratio	2000: 1
Resolution	WVGA (854 x 480)
Native Aspect Ratio	16: 9
Colour Support	16.7 million colours
Bulb type	LED
Bulb life cycle	Up to 20000 hour(s) - normal mode Up to 30000 hour(s) - economic mode
Power	AC 120/230 V
Power Consumption Operational	35 Watt
Weight	350 g

Manufacturer Warranty

2-year warranty

Extended Specification

General

Device Type	DLP projector
Built-in Devices	Lithium-ion battery (6700 mAh)

Projector

Brightness	200 lumens
Contrast Ratio	2000: 1
Image Size	63.5 cm - 254 cm
Projection Distance	0.6 m - 2.4 m
Throw Ratio	1.1:1
Resolution	WVGA (854 x 480) (native) / 1600 x 1200 (resized)
Native Aspect Ratio	16:9
Colour Support	16.7 million colours
Max Sync Rate (V x H)	60 Hz x 33.2 kHz
Bulb type	LED
Bulb life cycle	Up to 20000 hour(s) - normal mode Up to 30000 hour(s) - economic mode
Features	4:3 aspect ratio support

Lens

Focus Type	Manual
Lens Aperture	F/1.7

Video Input

Video Interfaces	HDMI
------------------	------

Expansion / Connectivity

Interfaces	1 x USB - 4 pin USB Type A 1 x HDMI - 19 pin HDMI Type A 1 x audio line-out
------------	---

Miscellaneous

Cables Included	1 x HDMI cable
-----------------	----------------

Power

Power Source	AC
Nominal Voltage	AC 120/230 V
Power Consumption Operational	35 Watt

Dimensions &Weight

Weight	350 g
--------	-------

Manufacturer Warranty

Service & Support	Limited warranty - 2 years - carry-in Limited warranty - 1 year
-------------------	--

Environmental Parameters

Min Operating Temperature	5 °C
Max Operating Temperature	40 °C
Humidity Range Operating	80%
Sound Emission	29 dBA
Sound Emission (Economic Mode)	25 dBA

What's in the box

Acer C200
HDMI cable

Product data is provided by CNET, we do not warrant the accuracy and completeness of the material contained in this data sheet