

Acer C202i(MR.JR011.001)

Acer C202i - DLP projector - LED - 300 lumens - WVGA (854 x 480) - 16:9



Main Specifications

Product Description	Acer C202i - DLP projector
Device Type	DLP projector
Built-in Devices	Lithium-ion battery (9000 mAh)
Brightness	300 lumens
Contrast Ratio	5000: 1
Resolution	WVGA (854 x 480)
Native Aspect Ratio	16:9
Colour Support	16.7 million colours
Bulb type	LED
Bulb life cycle	Up to 20000 hour(s) - normal mode Up to 30000 hour(s) - economic mode
Video Input	- MPEG-1, MPEG-2, MPEG-4, XviD, H.264, VC-1
Speakers	Speaker(s) - internal
Power	AC 120/230 V
Power Consumption Operational	30 Watt
Dimensions (WxDxH)	11.5 cm x 11.5 cm x 3.2 cm
Weight	350 g
Manufacturer Warranty	2-year warranty

Extended Specification

General

Device Type	DLP projector
Built-in Devices	Lithium-ion battery (9000 mAh)

Projector

Brightness	300 lumens
Contrast Ratio	5000: 1
Image Size	73.66 cm - 254 cm
Projection Distance	0.7 m - 2.9 m
Throw Ratio	1.3:1
Resolution	WVGA (854 x 480) (native) / 1600 x 1200 (resized)
Native Aspect Ratio	16:9
Colour Support	16.7 million colours

Max Sync Rate (V x H)	60 Hz x 33.2 kHz
Bulb type	LED
Bulb life cycle	Up to 20000 hour(s) - normal mode Up to 30000 hour(s) - economic mode
Features	4:3 aspect ratio support

Lens

Focus Type	Manual
Lens Aperture	F/1.6
Keystone Correction Direction	Horizontal,vertical
Vertical Keystone Correction	-20 / +20
Horizontal Keystone Correction	-20 / +20

Video Input

Video Interfaces	HDMI
Digital Video Format	MPEG-1,MPEG-2,MPEG-4,XviD,H.264,VC-1

Speakers

Type	Internal
Sound Output Mode	Mono
Output Power / Channel	2 Watt
Speakers	1 x mixed channel

Expansion / Connectivity

Interfaces	1 x USB - 4 pin USB Type A 1 x HDMI - 19 pin HDMI Type A 1 x headphones
------------	---

Miscellaneous

Included Accessories	Carrying case,tripod,wireless remote control,power adapter
----------------------	--

Power

Power Source	AC / battery
Nominal Voltage	AC 120/230 V
Power Consumption Operational	30 Watt

Dimensions &Weight

Width	11.5 cm
Depth	11.5 cm
Height	3.2 cm
Weight	350 g

Manufacturer Warranty

Service &Support	Limited warranty - 2 years Limited warranty - lamp - 1 year
------------------	--

Environmental Parameters

Min Operating Temperature 5 °C

Max Operating Temperature 40 °C

Humidity Range Operating 80%

Sound Emission 29 dBA

Sound Emission (Economic Mode) 25 dBA

Product data is provided by CNET, we do not warrant the accuracy and completeness of the material contained in this data sheet