



### Main

Range	TeSys
Accessory / separate part category	Protection accessory
Product or component type	Current limiting module
Function of module	Increasing the breaking capacity of a circuit breaker
Range compatibility	TeSys GV2
Product compatibility	GV2RT GV2ME GV2P GV2L
Mounting location	35 mm DIN rail
[Ie] rated operational current	32 A
[Ith] conventional free air thermal current	63 A conforming to IEC 60947-1
Operating threshold	1000 A
Breaking capacity	<= 100 kA depending on protective device
[Ue] rated operational voltage	690 V AC 50/60 Hz
[Ui] rated insulation voltage	690 V AC 50/60 Hz conforming to IEC 60947-1

### Complementary

Connections - terminals	Screw clamp terminals 1 x 1.5...25 mm <sup>2</sup> rigid Screw clamp terminals 2 x 1.5...10 mm <sup>2</sup> rigid Screw clamp terminals 1 x 1.5...25 mm <sup>2</sup> flexible without cable end Screw clamp terminals 2 x 1.5...10 mm <sup>2</sup> flexible without cable end Screw clamp terminals 1 x 1.5...16 mm <sup>2</sup> flexible with cable end Screw clamp terminals 2 x 1.5...4 mm <sup>2</sup> flexible with cable end
Tightening torque	2.2 N.m
Net weight	0.32 kg

### Offer Sustainability

RECh Regulation	<a href="#">REACH Declaration</a>
RECh free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes

Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

### Contractual warranty

Warranty	18 months
----------	-----------