



### Main

Range	TeSys
Product or component type	Capacitive delayed opening devices
Device short name	LAZR
Product compatibility	LC1F115...F630 LC1D09...D80
[Us] rated supply voltage	110...127 V AC

### Complementary

[Uc] control circuit voltage	155 V DC 174 V DC
Time delay range	0.4...5 s
Height	77 mm
Width	55 mm
Depth	114 mm
Net weight	0.215 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
RECh Regulation	<a href="#">RECh Declaration</a>
RECh free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

---

Circularity Profile	<a href="#">End of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

---

**Contractual warranty**

---

Warranty	18 months
----------	-----------

---