


PRODUCT-DETAILS

# CMS-121CA

## CMS-121CA Sensor




---

### General Information

Extended Product Type	CMS-121CA
Product ID	2CCA880221R0001
EAN	7612271453039
Catalog Description	CMS-121CA Sensor
Long Description	CMS-121CA 18mm Open-Core Sensor 40A

---

### Ordering

E-Number (Switzerland)	981912303
EAN	7612271453039
Minimum Order Quantity	1 piece
Customs Tariff Number	90303900

---

### Dimensions

Product Net Width	17.4 mm
Product Net Height	29 mm
Product Net Length	42 mm
Product Net Depth / Length	41 mm

Product Net Weight	11 g
--------------------	------

## Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	130 mm
Package Level 1 Height	75 mm
Package Level 1 Depth / Length	230 mm
Package Level 1 Gross Weight	83 g
Package Level 1 EAN	7612271453039

## Environmental

Ambient Air Temperature	Operation -25 ... +70 °C
RoHS Status	Following EU Directive 2002/95/EC August 18, 2005 and amendment

## Additional Information

Accuracy	Current Accuracy $\leq \pm 1\%$ F.S.
Frequency (f)	Rated Current 50 Hz
Measuring Range	Initial Value - Current 0.1 A End Value - Current 40 A
Mounting Type	Open core sensors 18 mm for cable mounting (universal use)
Output	Other
Product Main Type	CMS
Product Name	Sensor
RoHS Date	20170426

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information	2CCC481003C0201
Declaration of Conformity - CE	2CCC481017D0201
Environmental Information	2CCC481001D0202
Instructions and Manuals	9AKK106930A5216
RoHS Information	2CCC413008D0206

## Classifications

ETIM 4	EC002498 - Accessories for low-voltage switch technology
ETIM 5	EC002498 - Accessories for low-voltage switch technology
ETIM 6	EC002475 - Current value transformer
ETIM 7	EC002475 - Current value transformer
Object Classification Code	P
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

---

## Categories

---

Low Voltage Products and Systems → Modular DIN Rail Products → Energy Efficiency Devices → Circuit Monitoring Systems

