

PRODUCT-DETAILS

# PAFS21/BL/10M

## STD WGT BLK NYL COND NC21 10M BLK



### General Information

Extended Product Type	PAFS21/BL/10M
Product ID	7TCA296000R2199
EAN	5020963000874
Catalog Description	STD WGT BLK NYL COND NC21 10M BLK
Long Description	Standard Weight Conduit, Nominal Conduit Size 21mm, NW Conduit Size 17, Fine Conduit Pitch, Outside Diameter 21.2mm, Inside Diameter 16.5mm, Static Bend Radius 45mm, Reel Length 10 Meters, Polyamide (Nylon) 6, Black

### Ordering

EAN	5020963000874
Customs Tariff Number	3926909990

### Dimensions

Product Net Weight	1.32 lb 598.639 g
--------------------	----------------------

### Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	37 in 940 mm

Package Level 1 Height	1 in 25 mm
Package Level 1 Depth / Length	17 in 432 mm
Package Level 2 Units	1 piece
Package Level 3 Units	1 piece

## Additional Information

Application	Indoors / Outdoors - Light Industrial, Buildings & Machinery
Brand / Label	Adaptaflex
Color	Black
Flexibility	High
Inside Diameter	16.5 mm
Material	Polyamide/Nylon 6
Nominal Size	21 mm
Number of Batteries	0
Outside Diameter	21.2 mm
Product Name	CONDUIT
Product Type	Standard Weight Conduit with Fine Pitch
Radius	45 mm
Special Functions	High Fatigue Life, Self Extinguishing, Halogen Free
UPC	786210147437

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information	PAFS21/BL/10M
Declaration of Conformity - CE	9AKK107492A9618
Instructions and Manuals	PAFS21/BL/10M

## Classifications

ETIM 6	EC001175 - Corrugated plastic hose
ETIM 7	EC001175 - Corrugated plastic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5535 >> Electrical conduit

## Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

