

---

PRODUCT-DETAILS

# SP20/M20/A

## M20 FITTING FOR SP20



---

### General Information

Extended Product Type	SP20/M20/A
Product ID	7TCA296020R0149
EAN	5020963000010
Catalog Description	M20 FITTING FOR SP20
Long Description	Nickel Plated Brass Straight Fitting with Fixed External Thread, Nominal Conduit Size 20 Millimeters, Metric Thread Size M20

---

### Ordering

EAN	5020963000010
Customs Tariff Number	7412200035

---

### Dimensions

Product Net Weight	.067 lb 30.385 g
--------------------	---------------------

---

### Container Information

Package Level 1 Units	10 piece
Package Level 1 Width	1.5 in 38 mm
Package Level 1 Height	6.7 in

	170 mm
Package Level 1 Depth / Length	13.7 in 348 mm
Package Level 2 Units	300 piece
Package Level 2 Width	14 in 356 mm
Package Level 2 Height	6 in 152 mm
Package Level 2 Depth / Length	14 in 356 mm

### Additional Information

Application	For Insertion into Threaded Entries or Knockout to Connect Conduit
Brand / Label	Adaptaflex
Cable Entry Position	M20 Thread
Color	Metallic
Material	Brass
Number of Batteries	0
Product Name	brass fitting for conduit
Product Type	Conduit Fitting with Metric Threads
Size	1/2 Inch
Surface Finishing	Nickel Plated
UPC	786210247779

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	SP20/M20/A
Declaration of Conformity - CE	9AKK107492A9618
Instructions and Manuals	SP20/M20/A

### Classifications

ETIM 6	EC001180 - Screw connection for protective metallic hose
ETIM 7	EC001180 - Screw connection for protective metallic hose
UNSPSC	39121311
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4441 >> Electrical fittings

### Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

