

PRODUCT-DETAILS

SP25/M25/A

M25 FITTING FOR SP25



General Information

Extended Product Type	SP25/M25/A
Product ID	7TCA296020R0194
EAN	5020963000102
Catalog Description	M25 FITTING FOR SP25
Long Description	Nickel Plated Brass Straight Fitting with Fixed External Thread, Metric Thread Size M25

Ordering

EAN	5020963000102
Customs Tariff Number	7412200000

Dimensions

Product Net Weight	.004 lb 1.814 g
--------------------	--------------------

Container Information

Package Level 1 Units	10 piece
Package Level 1 Width	1.4 in 36 mm
Package Level 1 Height	1.3 in 33 mm

Package Level 1 Depth / Length	1.3 in 33 mm
Package Level 2 Units	250 piece
Package Level 2 Width	14 in 356 mm
Package Level 2 Height	14 in 356 mm
Package Level 2 Depth / Length	6 in 152 mm

Additional Information

Application	For Insertion into Threaded Entries or Knockout to Connect Conduit
Brand / Label	Adaptaflex
Cable Entry Position	M25 Thread
Color	Metallic
Material	Brass
Number of Batteries	0
Product Name	BRASS FITTING FOR CONDUIT
Product Type	Conduit Fitting with Metric Threads
Size	NC 25mm
Surface Finishing	Nickel Plated
UPC	786210249100

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	SP25/M25/A
Declaration of Conformity - CE	9AKK107492A9618
Instructions and Manuals	SP25/M25/A

Classifications

ETIM 6	EC001180 - Screw connection for protective metallic hose
ETIM 7	EC001180 - Screw connection for protective metallic hose
UNSPSC	39121311
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4441 >> Electrical fittings

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

