

PRODUCT-DETAILS

SP32/M32/B

M32 SWIVEL FITTING FOR SP32



General Information

Extended Product Type	SP32/M32/B
Product ID	7TCA296020R0247
EAN	5020963000478
Catalog Description	M32 SWIVEL FITTING FOR SP32
Long Description	Nickel Plated Brass Straight Fitting with Swivel External Thread, Nominal Conduit Size 32 Millimeters, Metric Thread Size M32

Ordering

EAN	5020963000478
Customs Tariff Number	7412200000

Dimensions

Product Net Weight	.13 lb 58.957 g
--------------------	--------------------

Container Information

Package Level 1 Units	2 piece
Package Level 1 Width	1.6 in 41 mm
Package Level 1 Height	2.2 in

	56 mm
Package Level 1 Depth / Length	1.8 in 46 mm
Package Level 2 Units	100 piece
Package Level 2 Width	1.6 in 41 mm
Package Level 2 Height	2.2 in 56 mm
Package Level 2 Depth / Length	1.8 in 46 mm

Additional Information

Application	For Insertion into Threaded Entries or Knockout to Connect Conduit
Brand / Label	Adaptaflex
Cable Entry Position	M32 Thread
Color	Metallic
Material	Brass
Number of Batteries	0
Product Name	brass fitting for conduit
Product Type	Conduit Fitting with Metric Threads
Size	1 Inch
Surface Finishing	Nickel Plated
UPC	786210249193

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	SP32/M32/B
Declaration of Conformity - CE	9AKK107492A9618
Instructions and Manuals	SP32/M32/B

Classifications

ETIM 6	EC001180 - Screw connection for protective metallic hose
ETIM 7	EC001180 - Screw connection for protective metallic hose
UNSPSC	39121311
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4441 >> Electrical fittings

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

