

PRODUCT-DETAILS

SPL25/M25/SAM

SS M25 FITTING FOR SAMHL25 CON



General Information

Extended Product Type	SPL25/M25/SAM
Product ID	7TCA296120R0045
EAN	5020963803895
Catalog Description	SS M25 FITTING FOR SAMHL25 CON
Long Description	Single Piece Conduit Fitting for Food and Beverage, Straight, Nominal Conduit Size 25mm, M25 Thread, 316 Stainless Steel

Ordering

EAN	5020963803895
Customs Tariff Number	7307290030

Dimensions

Product Net Weight	.37 lb 167.8 g
--------------------	-------------------

Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	1.75 in 44 mm
Package Level 2 Height	1.75 in

	44 mm
Package Level 2 Depth / Length	1.9 in 48 mm

Additional Information

Application	Indoor Splash Zone Areas or Food Processing Equipment
Brand / Label	Adaptaflex
Cable Entry Position	M25 Thread
Color	Metallic
Material	Stainless Steel
Number of Batteries	0
Product Name	SS LIQUID TIGHT CONDUIT FITTING
Product Type	Liquid Tight Non-Metallic Fitting
Size	NC 25mm
UPC	786210291345

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	SPL25/M25/SAM
Declaration of Conformity - CE	9AKK107492A9618
Instructions and Manuals	SPL25/M25/SAM

Classifications

ETIM 6	EC001180 - Screw connection for protective metallic hose
ETIM 7	EC001180 - Screw connection for protective metallic hose
UNSPSC	39121311
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4441 >> Electrical fittings

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

