
PRODUCT-DETAILS

LNSS/M63

M63 STAINLESS LOCKNUT



Product image
not available

General Information

Extended Product Type	LNSS/M63
Product ID	7TCA296120R0074
EAN	5020963807183
Catalog Description	M63 STAINLESS LOCKNUT
Long Description	Locknut, Size M63, Stainless Steel

Ordering

EAN	5020963807183
Customs Tariff Number	7307225000

Dimensions

Product Net Weight	.11 lb 49.887 g
--------------------	--------------------

Container Information

Package Level 2 Units	2 piece
Package Level 2 Width	1.5 in 38 mm
Package Level 2 Height	7 in 178 mm

Package Level 2 Depth /
Length

6 in
152 mm

Additional Information

Application	To Be Used with Fittings When Securing Into Knockouts
Brand / Label	Adaptaflex
Color	Metallic
Construction Material	316 Stainless Steel
Number of Batteries	0
Product Name	STAINLESS STEEL LOCKNUT
Product Type	Locknut with Metric Threads
Thread Size	M63
Thread Standard	Metric
UPC	786210311364

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	LNSS/M63
Declaration of Conformity - CE	9AKK107492A9618
Instructions and Manuals	LNSS/M63

Classifications

ETIM 6	EC000940 - Locknut for cable screw gland
ETIM 7	EC000940 - Locknut for cable screw gland
UNSPSC	31161716
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	2849 >> Locknuts

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems



Product image
not available