

PRODUCT-DETAILS

# XMM0606

## KFC STR CONNECTORS 32X32MM



### General Information

Extended Product Type	XMM0606
Product ID	7TCA297020R0472
EAN	5011949209169
Catalog Description	KFC STR CONNECTORS 32X32MM
Long Description	Liquid Tight Fitting for Covered Conduit, Straight with External Male Thread, Conduit Size 32mm, M32 Thread, Very High Mechanical and UV Protection, IP66, IP67 Ratings, Nickel Plated Brass with PVC Sleeve and Nylon Inserts

### Ordering

EAN	5011949209169
Customs Tariff Number	7412200090

### Dimensions

Product Net Weight	.304 lb 137.868 g
--------------------	----------------------

### Container Information

Package Level 2 Units	5 piece
Package Level 2 Width	1 in 25 mm

Package Level 2 Height	1 in 25 mm
Package Level 2 Depth / Length	1 in 25 mm

## Additional Information

Application	For Insertion Into Threaded Entries & Knockouts Using a Locknut to Secure
Brand / Label	Kopex
Color	Metallic
Insulation Material	IP66, 67 Rating
Material	Brass with Nylon Inserts and PVC Sleeve
Number of Batteries	0
Product Name	BASS FITTING FOR CONDUIT
Product Type	Straight Swivel Fitting with External Thread for Covered Conduit
Size	Conduit Size 32mm ; M32 Thread
Special Functions	Very High UV Protection and Mechanical Protection
Standards	UL E60625, BSI Kitemark KM-90009, Low Voltage Directive
Surface Finishing	Nickel Plated
UPC	786210264479

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information	XMM0606
Declaration of Conformity - CE	9AKK107492A9617
Instructions and Manuals	XMM0606

## Classifications

ETIM 6	EC001180 - Screw connection for protective metallic hose
ETIM 7	EC001180 - Screw connection for protective metallic hose
UNSPSC	39121420
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4585 >> Liquid tight connectors

## Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

