

PRODUCT-DETAILS

# BCM0505

## C12 CONNECTORS 25X25MM



Product image  
not available

---

### General Information

Extended Product Type	BCM0505
Product ID	7TCA297020R0049
EAN	5011949200289
Catalog Description	C12 CONNECTORS 25X25MM
Long Description	Fitting for Pliable Conduit, Straight with External Male Thread, Conduit Size 25mm, M25 Thread, Very High Mechanical and UV Protection, IP66, IP67 Ratings, Nickel Plated Brass with Nylon Seals

---

### Ordering

EAN	5011949200289
Customs Tariff Number	7412200035

---

### Dimensions

Product Net Weight	.2 lb 90.703 g
--------------------	-------------------

---

### Container Information

Package Level 2 Units	10 piece
Package Level 2 Width	1 in 25 mm

Package Level 2 Height	1 in 25 mm
Package Level 2 Depth / Length	1 in 25 mm

## Additional Information

Application	For Insertion Into Threaded Entries and Knockouts Using a Locknut to Secure
Brand / Label	Kopex
Color	Metallic
Insulation Class	IP66, 67
Material	Brass with Nylon Seals
Number of Batteries	0
Product Name	COPPER TUBE OR PIPE FITTINGS
Product Type	Fitting for Pliable Conduit
Size	Conduit Size 25mm ; M25 Thread
Special Functions	Very High Degree of UV and Mechanical Protection
Standards	BSI Kitemark KM-90009, Low Voltage Directive
Surface Finishing	Nickel Plated
Temperature Range	-40 to 130 °C
UPC	786210267777

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information	BCM0505
Declaration of Conformity - CE	9AKK107492A9617
Instructions and Manuals	BCM0505

## Classifications

ETIM 6	EC001180 - Screw connection for protective metallic hose
ETIM 7	EC001180 - Screw connection for protective metallic hose
UNSPSC	39121311
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4441 >> Electrical fittings

## Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems



Product image  
not available