

PRODUCT-DETAILS

EXQM0505

EXE LT STR 25MM FTNG N/P BR M25



Product image
not available

General Information

Extended Product Type	EXQM0505
Product ID	7TCA297120R0194
EAN	5011949001299
Catalog Description	EXE LT STR 25MM FTNG N/P BR M25
Long Description	Connector for Liquid Tight Conduit, Straight, Conduit Size 3/4 Inch/25mm, Thread Size M25, For Use in Industrial and Zone 2 Applications, IP66-67 Rating, Nickel Plated Brass

Ordering

EAN	5011949001299
Customs Tariff Number	7412200035

Dimensions

Product Net Weight	.22 lb 99.773 g
--------------------	--------------------

Container Information

Package Level 1 Units	2 piece
Package Level 2 Units	10 piece
Package Level 2 Width	14 in

	356 mm
Package Level 2 Height	6 in
	152 mm
Package Level 2 Depth / Length	14 in
	356 mm

Additional Information

Application	For Use in Industrial and Zone 2 Applications to Connect Conduit Systems
Brand / Label	Kopex
Color	Metallic
Insulation Material	IP66, 67 Rating
Material	Brass
Number of Batteries	0
Product Name	brass fitting for conduit
Product Type	Straight Connector for Liquid Tight Conduit
Size	Conduit Size 25mm ; M25 Thread
Standards	BS EN 61386
Surface Finishing	Nickel Plated
Temperature Range	-50 to 130 °C
UPC	786210276106

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	EXQM0505
Declaration of Conformity - CE	9AKK107492A9617
Instructions and Manuals	EXQM0505

Classifications

ETIM 6	EC001180 - Screw connection for protective metallic hose
ETIM 7	EC001180 - Screw connection for protective metallic hose
UNSPSC	39121420
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	4585 >> Liquid tight connectors

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems



Product image
not available