
PRODUCT-DETAILS

EXLB0430

FLEX CONDUIT 20MM OIL RESISTANT 30M



General Information

Extended Product Type	EXLB0430
Product ID	7TCA297120R0070
EAN	5011949001138
Catalog Description	FLEX CONDUIT 20MM OIL RESISTANT 30M
Long Description	Liquid Tight Metallic Conduit, Oil and Dilute Acid Resistant, Conduit Size 20mm, Minimum Bore 16mm, Reel Length 30 Meters, Galvanised Steel Core with Flame Retardant PVC Covering, Black

Ordering

EAN	5011949001138
Customs Tariff Number	8307106000

Dimensions

Product Net Weight	26.32 lb 11.937 kg
--------------------	-----------------------

Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	16.1 in 409 mm

Package Level 2 Height	5.9 in 150 mm
Package Level 2 Depth / Length	16.1 in 409 mm

Additional Information

Application	Connection for Conduit Systems when Oil and Acid Resistance is Needed
Brand / Label	Kopex
Color	Black
Inside Diameter	16 mm
Material	Galvanized Steel Core with Flame Retardant PVC Covering
Nominal Size	20 mm
Number of Batteries	0
Product Name	flexible metal conduit
Product Type	Liquid Tight Metallic Conduit
Special Functions	Flame Retardant PVC Covering
Standards	IEC 61386
UPC	786210287416

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	EXLB0430
Declaration of Conformity - CE	9AKK107492A9617
Instructions and Manuals	EXLB0430

Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5543 >> Liquid Tight Conduit

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

