

---

PRODUCT-DETAILS

# EXLT0310

## LFH FLEXIBLE CONDUIT 16MM 10M BLK



---

### General Information

Extended Product Type	EXLT0310
Product ID	7TCA297120R0133
EAN	5011949001930
Catalog Description	LFH FLEXIBLE CONDUIT 16MM 10M BLK
Long Description	Liquid Tight Metallic Conduit, Low Fire Hazard, Conduit Size 16mm, Minimum Bore 12.5mm, Reel Length 10 Meters, Galvanised Steel Core with LFH Coating, Black

---

### Ordering

EAN	5011949001930
Customs Tariff Number	8307106000

---

### Dimensions

Product Net Weight	6.49 lb 2.943 kg
--------------------	---------------------

---

### Container Information

Package Level 2 Units	1 piece
Package Level 2 Width	1 in 25 mm
Package Level 2 Height	1 in

	25 mm
Package Level 2 Depth / Length	1 in
	25 mm

---

### Additional Information

Application	Connection for Conduit Systems when Low Fire Hazard is Needed
Brand / Label	Kopex
Color	Black
Inside Diameter	12.5 mm
Material	Galvanized Steel Core with Low Fire Hazard Coating
Nominal Size	16 mm
Number of Batteries	0
Product Name	KOPEX
Product Type	Liquid Tight Metallic Conduit
Special Functions	Limited Fire Hazard, Zero Halogen (BS6425 Pt1)
Standards	LUL compliant (E1042A6)
UPC	786210264301

---

### Certificates and Declarations (Document Number)

Data Sheet, Technical Information	EXLT0310
Declaration of Conformity - CE	9AKK107492A9617
Instructions and Manuals	EXLT0310

---

### Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5543 >> Liquid Tight Conduit

---

### Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

